



Nameplate Specifications

Phase	3	Output HP	75 & 100 Hp
Output KW	56.0 & 75.0 kW	Voltage	200 & 200 V
Speed	1780 & 1780 rpm	Service Factor	1.0 & 1.0
Frame	365T	Enclosure	Drip Proof
Thermal Protection	No Protection	Efficiency	95 & 93.6 %
Ambient Temperature	40 °C	Frequency	60 & 60 Hz
Current	200 & 269 A	Power Factor	85
Duty	120/80 Starts/Hour	Insulation Class	F
Design Code	B	KVA Code	E
Drive End Bearing Size	6313	Opp Drive End Bearing Size	6311
UL	Recognized	CSA	Y
CE	Y	IP Code	22
Number of Speeds	1		

Technical Specifications

Electrical Type	Squirrel Cage Induction Run	Starting Method	Wye Start Delta Run
Poles	4	Rotation	Reversible
Resistance Main	.082 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	T	Assembly/Box Mounting	F1/F2 CAPABLE
Outline Drawing	XH2D1SS1-1648	Connection Drawing	A-EE7340-LN

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:06/22/2023