



### Nameplate Specifications

Output HP	5/2.22 Hp	Output KW	3.7 kW
Frequency	60 Hz	Voltage	200-230 V
Current	14.5-14/7.8-7.4 A	Speed	1775/1175 rpm
Service Factor	1.15	Phase	3
Duty	Continuous	Insulation Class	F
Frame	215T	Enclosure	Open Drip Proof
Thermal Protection	No Protection	Ambient Temperature	40 °C
UL	Recognized	CSA	Y
CE	Y	Number of Speeds	2

### Technical Specifications

Electrical Type	POLYPHASE	Starting Method	Across The Line
Poles	4/6	Rotation	Clockwise
Mounting	Rigid Base	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	Keyed	Overall Length	17.30 in
Frame Length	11.15 in	Shaft Diameter	1.375 in
Shaft Extension	3.47 in		
Connection Drawing	A-EE7317-CY	Outline Drawing	SS86500CY

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:11/28/2022