



### Nameplate Specifications

|                    |             |                     |              |
|--------------------|-------------|---------------------|--------------|
| Output HP          | 10.0/2.5 Hp | Output KW           | 7.5 kW       |
| Frequency          | 60 Hz       | Voltage             | 460 V        |
| Current            | 12.5/5.5 A  | Speed               | 1770/880 rpm |
| Service Factor     | 1.15        | Phase               | 3            |
| Duty               | Continuous  | Insulation Class    | F            |
| Frame              | S256T       | Enclosure           | Drip Proof   |
| Thermal Protection | None        | Ambient Temperature | 40 °C        |
| UL                 | Recognized  | CSA                 | Y            |
| CE                 | N           | Number of Speeds    | 2-2-VT       |

### Technical Specifications

|                       |              |                   |                             |
|-----------------------|--------------|-------------------|-----------------------------|
| Electrical Type       | Three Phase  | Starting Method   | Across The Line             |
| Poles                 | 4/ 8         | Rotation          | Reversible Counterclockwise |
| Mounting              | Rigid Base   | Drive End Bearing | Ball                        |
| Opp Drive End Bearing | Ball         | Frame Material    | Rolled Steel                |
| Shaft Type            | Keyed        | Overall Length    | 22.10 in                    |
| Frame Length          | 13.00 in     | Shaft Diameter    | 1.625 in                    |
| Shaft Extension       | 4.4 in       |                   |                             |
| Connection Drawing    | 80022806.PCX | Outline Drawing   | 80009201-S01                |

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:10/07/2021