

# PRODUCT INFORMATION PACKET



Model No: M521M2  
Catalog No: M521M2  
15 HP, General Purpose Motor, 3 phase, 1800 RPM, 200/230 V, S284T Frame, DP  
General Purpose Motors



Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.  
©2021 Regal Rexnord Corporation, All Rights Reserved. MC017097E





### Nameplate Specifications

Output HP	15.0/6.7 Hp	Output KW	11.2 kW
Frequency	60 Hz	Voltage	200/230 V
Current	40-36/20-19 A	Speed	1775/1175 rpm
Service Factor	1.15	Phase	3
Duty	Continuous	Insulation Class	F
Frame	S284T	Enclosure	Drip Proof
Thermal Protection	None	Ambient Temperature	40 °C
UL	Recognized	CSA	Y
CE	N	Number of Speeds	2-2-VT

### Technical Specifications

Electrical Type	Three Phase	Starting Method	Across The Line
Poles	4/6	Rotation	Reversible Counterclockwise
Mounting	Rigid Base	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	Keyed	Overall Length	24.22 in
Frame Length	14.00 in	Shaft Diameter	1.875 in
Shaft Extension	5.09 in		
Connection Drawing	80022806.PCX	Outline Drawing	80009201-S01

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:10/07/2021

