



Nameplate Specifications

Output HP	3 Hp	Output KW	2.2 kW
Frequency	60 Hz	Voltage	230/115 V
Current	16.1/32 A	Speed	3500 rpm
Service Factor	1.15	Phase	1
Duty	Continuous	Insulation Class	F
Frame	182JM	Enclosure	Drip Proof
Thermal Protection	No Protection	Ambient Temperature	60 °C
UL	Recognized	CSA	Y
CE	Y	Number of Speeds	1

Technical Specifications

Electrical Type	Capacitor Start	Starting Method	Across The Line
Poles	2	Rotation	Selective Counterclockwise
Mounting	Rigid Base	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	Keyed	Overall Length	15.32 in
Frame Length	9.50 in	Shaft Diameter	1.250 in
Shaft Extension	4.245 in		
Connection Drawing	005062.01CY	Outline Drawing	035557CY

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:11/28/2022