



### Nameplate Specifications

|                    |             |                     |                 |
|--------------------|-------------|---------------------|-----------------|
| Output HP          | 3 Hp        | Output KW           | 2.2 kW          |
| Frequency          | 60 Hz       | Voltage             | 230/115 V       |
| Current            | 16.8/33.5 A | Speed               | 1747 rpm        |
| Service Factor     | 1.15        | Phase               | 1               |
| Duty               | Continuous  | Insulation Class    | F               |
| Frame              | 184JM       | Enclosure           | Open Drip Proof |
| Thermal Protection | No          | Ambient Temperature | 40 °C           |
| UL                 | Recognized  | CSA                 | Y               |
| CE                 | Y           | Number of Speeds    | 1               |

### Technical Specifications

|                       |                 |                    |                  |
|-----------------------|-----------------|--------------------|------------------|
| Electrical Type       | Capacitor Start | Starting Method    | Across The Line  |
| Poles                 | 4               | Rotation           | Counterclockwise |
| Mounting              | Rigid Base      | Drive End Bearing  | Ball             |
| Opp Drive End Bearing | Ball            | Frame Material     | Rolled Steel     |
| Shaft Type            | Keyed           | Overall Length     | 15.95 in         |
| Frame Length          | 10.00 in        | Shaft Diameter     | 1.250 in         |
| Shaft Extension       | 4.25 in         |                    |                  |
| Outline Drawing       | 035890CY        | Connection Drawing | 005062.01CY      |

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:10/12/2021