



Nameplate Specifications

Output HP	5 Hp	Output KW	3.7 kW
Frequency	60 Hz	Voltage	230 V
Current	22.7 A	Speed	3530 rpm
Service Factor	1.15	Phase	1
Duty	Continuous	Insulation Class	F
Frame	184JM	Enclosure	Open Drip Proof
Thermal Protection	No Protection	Ambient Temperature	40 °C
UL	Recognized	CSA	Y
CE	Y	Number of Speeds	1

Technical Specifications

Electrical Type	Capacitor Start	Starting Method	Across The Line
Poles	2	Rotation	Counterclockwise
Mounting	Rigid Base	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	Keyed	Overall Length	17.95 in
Frame Length	12.00 in	Shaft Diameter	1.250 in
Shaft Extension	4.25 in		
Connection Drawing	005033.01CY	Outline Drawing	035890CY

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:11/28/2022