



Nameplate Specifications

Output HP	7.5 Hp	Output KW	5.6 kW
Frequency	60 Hz	Voltage	230 V
Current	34.5 A	Speed	1733 rpm
Service Factor	1.15	Phase	1
Duty	Continuous	Insulation Class	F
Frame	215JP	Enclosure	Drip Proof
Thermal Protection	No	Ambient Temperature	40 °C
UL	Recognized	CSA	Y
Number of Speeds	1		

Technical Specifications

Electrical Type	Capacitor Start Capacitor Run	Starting Method	Across The Line
Poles	4	Rotation	Selective Counterclockwise
Mounting	Rigid Base	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	Keyed	Overall Length	23.79 in
Frame Length	11.15 in	Shaft Diameter	1.750 in
Shaft Extension	8.43 in		
Connection Drawing	A-EE9048MF-CY	Outline Drawing	037644CY

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:10/07/2021