



Nameplate Specifications

Output HP	1.0-.25 Hp	Output KW	0.75 kW
Frequency	60 Hz	Voltage	200-230 V
Current	3.5-3.4/1.5-1.6 A	Speed	1745/850 rpm
Service Factor	1.15	Phase	3
Duty	Continuous	Insulation Class	B
Frame	L143T	Enclosure	Drip Proof
Thermal Protection	No Protection	Ambient Temperature	40 °C
UL	Recognized	CSA	Y
CE	N	Number of Speeds	2-1-VT

Technical Specifications

Electrical Type	Polyphase, Induction Type, Multi-Speed	Starting Method	Across The Line
Poles	4/ 8	Rotation	Reversible Counterclockwise
Mounting	Rigid Base	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	Keyed	Overall Length	12.06 in
Frame Length	6.25 in	Shaft Diameter	0.875 in
Shaft Extension	2.31 in		
Outline Drawing	114501-S01	Connection Drawing	17050625.PCX

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:11/29/2022