



Nameplate Specifications

Output HP	2/0.9 Hp	Output KW	1.5 kW
Frequency	60 Hz	Voltage	200-230 V
Current	6.6-6.4/3.8-3.9 A	Speed	1765/1175 rpm
Service Factor	1.15	Phase	3
Duty	Continuous	Insulation Class	F
Frame	182T	Enclosure	Open Drip Proof
Thermal Protection	No	Ambient Temperature	40 °C
UL	Recognized	CSA	Y
CE	Y	Number of Speeds	2-1-VT

Technical Specifications

Electrical Type	Polyphase	Starting Method	Across The Line
Poles	4/6	Rotation	Reversible
Mounting	Rigid Base	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	Keyed	Overall Length	12.69 in
Frame Length	8.50 in	Shaft Diameter	1.125 in
Shaft Extension	2.81 in		
Outline Drawing	035539CY	Connection Drawing	005046.01CY

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:10/07/2021