



Nameplate Specifications

Output HP	7.5/3.3 Hp	Output KW	5.6 kW
Frequency	60 Hz	Voltage	200-230 V
Current	20.3-18/10.8-9.6 A	Speed	1770/1180 rpm
Service Factor	1.15	Phase	3
Duty	Continuous	Insulation Class	F
Frame	215T	Enclosure	Drip Proof
Thermal Protection	No	Ambient Temperature	40 °C
UL	Recognized	CSA	Y
CE	Y	Number of Speeds	2

Technical Specifications

Electrical Type	Polyphase	Starting Method	Across The Line
Poles	4/6	Rotation	Reversible
Mounting	Rigid Base	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	Keyed	Overall Length	21.06 in
Frame Length	15.45 in	Shaft Diameter	1.375 in
Shaft Extension	3.47 in		
Outline Drawing	SS86500CY	Connection Drawing	A-EE7317-CY

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:10/12/2021