



### Nameplate Specifications

Output HP	7.5 Hp	Output KW	5.6 kW
Frequency	60 Hz	Voltage	230 V
Current	37 A	Speed	3470 rpm
Service Factor	1.15	Phase	1
Duty	Continuous	Insulation Class	F
Frame	213JP	Enclosure	Open Drip Proof
Thermal Protection	No Protection	Ambient Temperature	40 °C
UL	Recognized	CSA	Y
Number of Speeds	1		

### Technical Specifications

Electrical Type	Capacitor Start	Starting Method	Across The Line
Poles	2	Rotation	Counterclockwise
Mounting	Rigid Base	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	Keyed	Overall Length	22.29 in
Frame Length	9.65 in	Shaft Diameter	1.750 in
Shaft Extension	8.43 in		
Outline Drawing	037644CY	Connection Drawing	A-EE7090JR-CY

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:11/29/2022