

Nameplate Specifications

| | | | |
|------------------------|---------------|----------------------------|-----------------------------|
| Output HP | 5.50 Hp | Output KW | 4.0 kW |
| Frequency | 50 Hz | Voltage | 380 V |
| Current | 7.5 A | Speed | 2932 rpm |
| Service Factor | 1 | Phase | 3 |
| Efficiency | 90 % | Power Factor | 0.91 |
| Duty | S1 | Insulation Class | F |
| Frame | 112M | Enclosure | Totally Enclosed Fan Cooled |
| Thermal Protection | No Protection | Ambient Temperature | 40 °C |
| Drive End Bearing Size | 6306 | Opp Drive End Bearing Size | 6206 |
| UL | No | CSA | No |
| CE | YES | IP Code | 55 |
| Number of Speeds | 1 | Efficiency Class | IE4 |

Technical Specifications

| | | | |
|-----------------------|---------------|-----------------------|----------------|
| Electrical Type | Squirrel Cage | Starting Method | Direct On Line |
| Poles | 2 | Rotation | Bi-Directional |
| Mounting | B5 | Motor Orientation | Horizontal |
| Drive End Bearing | 2z-C3 | Opp Drive End Bearing | 2z-C3 |
| Frame Material | Cast Iron | Shaft Type | Keyed |
| Overall Length | 399 mm | Frame Length | 174 mm |
| Shaft Diameter | 28 mm | Shaft Extension | 60 mm |
| Assembly/Box Mounting | Top | | |
| Outline Drawing | 0211200264 | Connection Drawing | 8442000085 |