

Nameplate Specifications

| | | | |
|------------------------|---------------|----------------------------|-----------------------------|
| Output HP | 30 Hp | Output KW | 22.0 kW |
| Frequency | 50 Hz | Voltage | 380 V |
| Current | 45.0 A | Speed | 986 rpm |
| Service Factor | 1 | Phase | 3 |
| Efficiency | 93.7 % | Power Factor | 0.8 |
| Duty | S1 | Insulation Class | F |
| Frame | 200L | Enclosure | Totally Enclosed Fan Cooled |
| Thermal Protection | No Protection | Ambient Temperature | 40 °C |
| Drive End Bearing Size | 6312 | Opp Drive End Bearing Size | 6212 |
| UL | No | CSA | No |
| CE | YES | IP Code | 55 |
| Number of Speeds | 1 | Efficiency Class | IE4 |

Technical Specifications

| | | | |
|-----------------------|---------------|-----------------------|----------------|
| Electrical Type | Squirrel Cage | Starting Method | Direct On Line |
| Poles | 6 | Rotation | Bi-Directional |
| Mounting | B35 | Motor Orientation | Horizontal |
| Drive End Bearing | C3 | Opp Drive End Bearing | C3 |
| Frame Material | Cast Iron | Shaft Type | Keyed |
| Overall Length | 769 mm | Frame Length | 370 mm |
| Shaft Diameter | 55 mm | Shaft Extension | 110 mm |
| Assembly/Box Mounting | R Side | | |
| Connection Drawing | 8442000085 | Outline Drawing | 0220000523 |