

# PRODUCT INFORMATION PACKET

**marathon®**  
Motors

Model No: QCA0221A1121GAA001

Catalog No: QCA0221A1121GAA001

TerraMAX® Cast Iron Motor, 30 HP, 3 Ph, 50 Hz, 400 V, 3000 RPM, 180M Frame, TEFC



Regal and Marathon are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2022 Regal Rexnord Corporation, All Rights Reserved. MC017097E

**RegalRexnord**


### Nameplate Specifications


|                        |               |                            |                             |
|------------------------|---------------|----------------------------|-----------------------------|
| Output HP              | 30 Hp         | Output KW                  | 22.0 kW                     |
| Frequency              | 50 Hz         | Voltage                    | 400 V                       |
| Current                | 38.1 A        | Speed                      | 2963 rpm                    |
| Service Factor         | 1             | Phase                      | 3                           |
| Efficiency             | 94 %          | Power Factor               | 0.89                        |
| Duty                   | S1            | Insulation Class           | F                           |
| Frame                  | 180M          | Enclosure                  | Totally Enclosed Fan Cooled |
| Thermal Protection     | No Protection | Ambient Temperature        | 40 °C                       |
| Drive End Bearing Size | 6311          | Opp Drive End Bearing Size | 6211                        |
| UL                     | No            | CSA                        | No                          |
| CE                     | Yes           | IP Code                    | 55                          |
| Number of Speeds       | 1             | Efficiency Class           | IE4                         |

### Technical Specifications

|                       |               |                       |                |
|-----------------------|---------------|-----------------------|----------------|
| Electrical Type       | Squirrel Cage | Starting Method       | Direct On Line |
| Poles                 | 2             | Rotation              | Bi-Directional |
| Mounting              | B5            | Motor Orientation     | Horizontal     |
| Drive End Bearing     | 2z-C3         | Opp Drive End Bearing | 2z-C3          |
| Frame Material        | Cast Iron     | Shaft Type            | Keyed          |
| Overall Length        | 750 mm        | Frame Length          | 366 mm         |
| Shaft Diameter        | 48 mm         | Shaft Extension       | 110 mm         |
| Assembly/Box Mounting | Top           |                       |                |
| Connection Drawing    | 8442000085    | Outline Drawing       | 0218000504     |

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:12/01/2022




|                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                          |  |                        |  |                   |  |                           |  |                                                                                       |  |                                                                   |                              |  |                |  |                 |
|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|------------------------|--|-------------------|--|---------------------------|--|---------------------------------------------------------------------------------------|--|-------------------------------------------------------------------|------------------------------|--|----------------|--|-----------------|
| DRAWING REVISION<br>C                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                    |  | REVISION BY<br>S.MUDDA |  | DATE<br>26/8/2020 |  | <div></div>               |  | DRAWN BY<br>SDV                                                                       |  | <div><div>REGAL™</div><div>Regal Beloit America, Inc.</div></div> |                              |  |                |  |                 |
| ECO<br>ECO-0190270                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                       |  | APPROVED BY<br>JAY     |  | DATE<br>26/8/2020 |  |                           |  | DATE<br>7-05-2014                                                                     |  |                                                                   |                              |  |                |  |                 |
| ECO DESCRIPTION<br>CONFIGURATIONS ADDED TO THE 3D MODEL                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                  |  |                        |  |                   |  |                           |  | APPROVED BY<br>SBD                                                                    |  | DESCRIPTION<br><div>OUTLINE</div> <div>180L-2-8P-B5</div>         |                              |  |                |  |                 |
|                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                          |  |                        |  |                   |  |                           |  | DATE<br>7-05-2014                                                                     |  |                                                                   |                              |  |                |  |                 |
| COPYRIGHT REGAL BELOIT AMERICA, INC. ALL RIGHTS RESERVED.<br>PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF<br>REGAL BELOIT AMERICA, INC. ("OWNER") AND CONTAINS OWNER'S PROPRIETARY<br>INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED,<br>BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED<br>TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT<br>AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL<br>BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN<br>RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS. |  |                        |  |                   |  |                           |  | REFERENCE                                                                             |  | MATERIAL                                                          |                              |  | PROCESS/FINISH |  |                 |
|                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                          |  |                        |  |                   |  | THIRD ANGLE<br>PROJECTION |  |  |  | SIZE<br>B                                                         | DRAWING NUMBER<br>0218000504 |  |                |  | SHEET<br>1 OF 1 |

RIGHTS RESERVED. Uncontrolled Copy

### ECO DESCRIPTION

## GEOMETRIC TOLERANCE

|            |         |      |
|------------|---------|------|
| LINEAR DIM | >0~6    | ±0.1 |
|            | >6~30   | ±0.2 |
|            | >30~120 | ±0.3 |



1. PRESSURE-SENSITIVE ADHESIVE COATED PAPER ON THE BACK OF SELF-ADHESIVE.
2. AT THE END OF YELLOW, WORDS, SYMBOLS, LETTERS ARE BLACK, BORDER IS BLACK.
3. THE TOLERANCE OF THE LINEAR SIZE OF THE TOLERANCE WITHOUT THE TOLERANCE BY THE TABLE.

8WD.442.2017

|                                                                                     |                        |                                                                                                                 |                                     |                |
|-------------------------------------------------------------------------------------|------------------------|-----------------------------------------------------------------------------------------------------------------|-------------------------------------|----------------|
|  | DRAWN BY<br>SN         |  Regal Beloit America, Inc. |                                     |                |
|                                                                                     | DATE<br>16/12/2016     |                                                                                                                 |                                     |                |
|                                                                                     | APPROVED BY<br>SBD     | DESCRIPTION<br><b>CONN DIAGRAM-NAMEPLATE</b>                                                                    |                                     |                |
|                                                                                     | DATE<br>16/12/2016     |                                                                                                                 |                                     |                |
|                                                                                     | REFERENCE              | MATERIAL                                                                                                        |                                     | PROCESS/FINISH |
|                                                                                     | THIRD ANGLE PROJECTION | SIZE<br><b>A</b>                                                                                                | DRAWING NUMBER<br><b>8442000085</b> |                |

**Model No.** QCA0221A1121GAA001

| U<br>(V) | Δ / Y<br>Conn | f<br>[Hz] | P<br>[kW] | P<br>[hp] | I<br>[A] | n<br>[RPM] | T<br>[Nm] | IE<br>Class | % EFF at __ load |    |       |       | PF at __ load |       |       | I <sub>A</sub> /I <sub>N</sub><br>[pu] | T <sub>A</sub> /T <sub>N</sub><br>[pu] | T <sub>K</sub> /T <sub>N</sub><br>[pu] |
|----------|---------------|-----------|-----------|-----------|----------|------------|-----------|-------------|------------------|----|-------|-------|---------------|-------|-------|----------------------------------------|----------------------------------------|----------------------------------------|
|          |               |           |           |           |          |            |           |             | 5/4FL            | FL | 3/4FL | 1/2FL | FL            | 3/4FL | 1/2FL |                                        |                                        |                                        |
| 400      | Δ             | 50        | 22        | 30        | 38.1     | 2963       | 72.10     | IE4         | -                | 94 | 94    | 92.5  | 0.89          | 0.86  | 0.77  | 7.4                                    | 2.2                                    | 3.6                                    |
|          |               |           |           |           |          |            |           |             |                  |    |       |       |               |       |       |                                        |                                        |                                        |

|                                  |                    |                                           |                                            |
|----------------------------------|--------------------|-------------------------------------------|--------------------------------------------|
| Motor type                       | QCA                | Degree of protection                      | IP 55                                      |
| Enclosure                        | TEFC               | Mounting type                             | IM B5                                      |
| Frame Material                   | Cast Iron          | Cooling method                            | IC 411                                     |
| Frame size                       | 180M               | Motor weight - approx.                    | 257 kg                                     |
| Duty                             | S1                 | Gross weight - approx.                    | 277 kg                                     |
| Voltage variation *              | ± 10%              | Motor inertia                             | 0.1801 kgm <sup>2</sup>                    |
| Frequency variation *            | ± 5%               | Load inertia                              | Customer to Provide                        |
| Combined variation *             | 10%                | Vibration level                           | 2.2 mm/s                                   |
| Design                           | N                  | Noise level ( 1meter distance from motor) | 72 dB(A)                                   |
| Service factor                   | 1.0                | No. of starts hot/cold/Equally spread     | 2/3/4                                      |
| Insulation class                 | F                  | Starting method                           | DOL                                        |
| Ambient temperature              | -20 to +40 °C      | Type of coupling                          | Direct                                     |
| Temperature rise (by resistance) | 80 [ Class B ] K   | LR withstand time (hot/cold)              | 15/30 s                                    |
| Altitude above sea level         | 1000 meter         | Direction of rotation                     | Bi-directional                             |
| Hazardous area classification    | NA                 | Standard rotation                         | Clockwise form DE                          |
| Zone classification              | NA                 | Paint shade                               | RAL 5014                                   |
| Gas group                        | NA                 | Accessories                               |                                            |
| Temperature class                | NA                 | Accessory - 1                             | PTC 150°C                                  |
| Rotor type                       | Aluminum Die cast  | Accessory - 2                             | -                                          |
| Bearing type                     | Anti-friction ball | Accessory - 3                             | -                                          |
| DE / NDE bearing                 | 6311-2Z / 6211-2Z  | Terminal box position                     | TOP                                        |
| Lubrication method               | Greased for life   | Maximum cable size/conduit size           | 1R x 3C x 35mm <sup>2</sup> /2 X M32 x 1.5 |
| Type of grease                   | NA                 | Auxiliary terminal box                    | NA                                         |

I<sub>A</sub>/I<sub>N</sub> - Locked Rotor Current / Rated Current

T<sub>K</sub>/T<sub>N</sub> - Breakdown Torque / Rated Torque

T<sub>A</sub>/T<sub>N</sub> - Locked Rotor Torque / Rated Torque

**NOTE**

All performance values at rated voltage and frequency.

All performance parameters are subjected to standard tolerance as per IEC 60034-1

\* Voltage, Frequency and combined variation are as per IEC60034-1

Technical data are subject to change. There may be slight variations between calculated values in this datasheet and the motor nameplate figures.


| Efficiency | Europe         | China | India | Aus/Nz            | Brazil | Global IEC     |
|------------|----------------|-------|-------|-------------------|--------|----------------|
| Standards  | IEC 60034-30-1 | -     | -     | AS/NZ 1359:5:2004 | -      | IEC 60034-30-1 |

**Model No.** QCA0221A1121GAA001


| Enclosure | U<br>(V) | Δ / Y<br>Conn | f<br>(Hz) | P<br>[kW] | P<br>[hp] | I<br>[A] | n<br>[RPM] | T<br>[kgm] | T<br>[Nm] | IE<br>Class | Amb<br>[°C] | Duty | Elevation<br>[m] | Inertia<br>[kg-m <sup>2</sup> ] | Weight<br>[kg] |
|-----------|----------|---------------|-----------|-----------|-----------|----------|------------|------------|-----------|-------------|-------------|------|------------------|---------------------------------|----------------|
| TEFC      | 400      | Δ             | 50        | 22        | 30        | 38.1     | 2963       | 7.35       | 72.10     | IE4         | 40          | S1   | 1000             | 0.1801                          | 257            |

**Motor Load Data**

| Load Point   |       | NL   | 1/4FL | 1/2FL | 3/4FL | FL   | 5/4FL |
|--------------|-------|------|-------|-------|-------|------|-------|
| Current      | A     | 12.6 | 15.7  | 22.7  | 30.5  | 38.1 |       |
| Torque       | Nm    | 0.0  | 17.9  | 35.8  | 53.9  | 72.1 |       |
| Speed        | r/min | 3000 | 2991  | 2982  | 2973  | 2963 |       |
| Efficiency   | %     | 0.0  | 88.4  | 92.5  | 94.0  | 94.0 |       |
| Power Factor | %     | 7.8  | 58.2  | 77.0  | 86.0  | 89.0 |       |

**Performance vs Load Chart**

**Motor Speed Torque Data**

| Load Point |       | LR    | P-Up  | BD    | Rated | NL   |
|------------|-------|-------|-------|-------|-------|------|
| Speed      | r/min | 0     | 600   | 2725  | 2963  | 3000 |
| Current    | A     | 281.9 | 253.7 | 178.4 | 38.1  | 12.6 |
| Torque     | pu    | 2.2   | 1.9   | 3.6   | 1     | 0    |

**Starting Characteristics Chart**

**NOTE** Refer data sheet for applicable standard and tolerances on performance parameters


 Issued By  
Issued Date

**Model No.** QCA0221A1121GAA001

| Enclosure | U<br>(V) | $\Delta$ / Y<br>Conn | f<br>[Hz] | P<br>[kW] | P<br>[hp] | I<br>[A] | n<br>[rpm] | T<br>[kgm] | T<br>[Nm] | IE<br>Class | Amb<br>[°C] | Duty | Elevation<br>[m] | Inertia<br>[kg-m <sup>2</sup> ] | Weight<br>[kg] |
|-----------|----------|----------------------|-----------|-----------|-----------|----------|------------|------------|-----------|-------------|-------------|------|------------------|---------------------------------|----------------|
| TEFC      | 400      | $\Delta$             | 50        | 22        | 30        | 38.1     | 2963       | 7.35       | 72.10     | IE4         | 40          | S1   | 1000             | 0.1801                          | 257            |

**Motor Speed Torque Data**

| Load     | FL      | I <sub>1</sub> | I <sub>2</sub> | I <sub>3</sub> | I <sub>4</sub> | I <sub>5</sub> | LR  |
|----------|---------|----------------|----------------|----------------|----------------|----------------|-----|
| TWT Hot  | s 10000 | 56             | 37             | 30             | 25             | 20             | 15  |
| TWT Cold | s 10000 | 111            | 74             | 65             | 50             | 45             | 30  |
| Current  | pu      | 1              | 2              | 4              | 5              | 5.5            | 7.4 |

**Thermal Characteristics Chart**

**NOTE** Refer data sheet for applicable standard and tolerances on performance parameters

 Issued By  
Issued Date