

### Nameplate Specifications

Output HP	10.0-14.0 Hp	Output KW	7.5 kW
Frequency	60 Hz	Voltage	230/460 V
Current	36/18 A	Speed	3460 rpm
Service Factor	1	Phase	3
Duty	Continuous	Insulation Class	F
Frame	F215TZ	Enclosure	Totally Enclosed Air Over
Thermal Protection	No Protection	Ambient Temperature	50 °C
UL	Recognized	CSA	Y
CE	N	Number of Speeds	1

### Technical Specifications

Electrical Type	Polyphase, Induction Type, Single Or Dual Voltage	Starting Method	Across The Line
Poles	2	Rotation	Reversible
Mounting	Rigid Base	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	Keyed	Overall Length	19.98 in
Frame Length	9.00 in	Shaft Diameter	1.125 in
Shaft Extension	4.50 in		
Connection Drawing	80022802	Outline Drawing	R327M2-S01

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:09/08/2022