



Nameplate Specifications

Output HP	10 Hp	Output KW	7.5 kW
Frequency	50 Hz	Voltage	220/440 V
Current	25.3/12.7 A	Speed	3530 rpm
Service Factor	1.15	Phase	3
Duty	Continuous	Insulation Class	F
Frame	213TDZ	Enclosure	Drip Proof
Thermal Protection	No Protection	Ambient Temperature	40 °C
UL	Recognized	CSA	Y
CE	Y	Number of Speeds	1

Technical Specifications

Electrical Type	Squirrel Cage Induction Run	Starting Method	Across The Line
Poles	2	Rotation	Reversible
Mounting	Special/Non-Standard	Motor Orientation	Horizontal
Drive End Bearing	Ball	Opp Drive End Bearing	Ball
Frame Material	Rolled Steel	Shaft Type	7/8 Keyed
Overall Length	16.54 in	Frame Length	9.65 in
Shaft Diameter	1.000 in	Shaft Extension	3 in
Connection Drawing	005010.01	Outline Drawing	OLR338M2A

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:01/25/2023