

Nameplate Specifications

Phase	3	Output HP	75 & 60 Hp
Output KW	55.0 & 45.0 kW	Voltage	230/460 & 200/400 V
Speed	1190 & 990 r/min	Service Factor	1.15 & 1.15
Frame	280M	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	No Protection	Efficiency	94.5 & 93.7 %
Ambient Temperature	40 °C	Frequency	60 & 50 Hz
Current	174/87 & 166/83 A	Power Factor	84
Duty	Continuous	Insulation Class	F
Design Code	N (IEC)	KVA Code	G
Drive End Bearing Size	6317	Opp Drive End Bearing Size	6317
UL	Recognized	CSA	N
CE	Y	IP Code	55
Number of Speeds	1	Efficiency Class	IE3

Technical Specifications

Electrical Type	Squirrel Cage Inverter Rated	Starting Method	Line Or Inverter
Poles	6	Rotation	Reversible
Resistance Main	.07 O	Mounting	B3
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Cast Iron
Shaft Type	IEC	Overall Length	43.74 in
Frame Length	23.62 in	Shaft Diameter	2.953 in
Shaft Extension	5.51 in	Assembly/Box Mounting	F3
Inverter Load	CONSTANT 2:1/VARIABLE 10:1		
Connection Drawing	8442000715	Outline Drawing	SS557728

