

### Nameplate Specifications

|                        |               |                            |                             |
|------------------------|---------------|----------------------------|-----------------------------|
| Output HP              | 150 Hp        | Output KW                  | 110.0 kW                    |
| Frequency              | 50 Hz         | Voltage                    | 400 V                       |
| Current                | 189.5 A       | Speed                      | 2983 rpm                    |
| Service Factor         | 1             | Phase                      | 3                           |
| Efficiency             | 95.2 %        | Power Factor               | 0.88                        |
| Duty                   | S1            | Insulation Class           | F                           |
| Frame                  | 315S          | Enclosure                  | Totally Enclosed Fan Cooled |
| Thermal Protection     | No Protection | Ambient Temperature        | 40 °C                       |
| Drive End Bearing Size | 6316          | Opp Drive End Bearing Size | 6316                        |
| UL                     | No            | CSA                        | No                          |
| CE                     | Yes           | IP Code                    | 55                          |
| Efficiency Class       | IE3           |                            |                             |

### Technical Specifications

|                       |               |                       |                |
|-----------------------|---------------|-----------------------|----------------|
| Electrical Type       | Squirrel Cage | Starting Method       | Direct On Line |
| Poles                 | 2             | Rotation              | Bi-Directional |
| Mounting              | B3            | Motor Orientation     | Horizontal     |
| Drive End Bearing     | C3            | Opp Drive End Bearing | C3             |
| Frame Material        | Cast Iron     | Shaft Type            | Keyed          |
| Overall Length        | 1176 mm       | Frame Length          | 729 mm         |
| Shaft Diameter        | 65 mm         | Shaft Extension       | 140 mm         |
| Assembly/Box Mounting | R Side        |                       |                |
| Outline Drawing       | 0231501360    | Connection Drawing    | 8442000085     |