

PRODUCT INFORMATION PACKET

marathon®
Motors

Model No: TCA7P53A3133GACD01

Catalog No: TCA7P53A3133GACD01

Cast Iron Motor, 10 HP, 3 Ph, 50 Hz, 415 V, 1000 RPM, 160M Frame, TEFC



Regal and Marathon are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2022 Regal Rexnord Corporation, All Rights Reserved. MC017097E

RegalRexnord

Nameplate Specifications

| | | | |
|------------------------|---------------|----------------------------|-----------------------------|
| Output HP | 10 Hp | Output KW | 7.5 kW |
| Frequency | 50 Hz | Voltage | 415 V |
| Current | 14.8 A | Speed | 977 rpm |
| Service Factor | 1 | Phase | 3 |
| Efficiency | 89.1 % | Power Factor | 0.79 |
| Duty | S1 | Insulation Class | F |
| Frame | 160M | Enclosure | Totally Enclosed Fan Cooled |
| Thermal Protection | No Protection | Ambient Temperature | 50 °C |
| Drive End Bearing Size | 6309 | Opp Drive End Bearing Size | 6209 |
| UL | No | CSA | No |
| CE | Yes | IP Code | 55 |
| Number of Speeds | 1 | Efficiency Class | IE3 |

Technical Specifications

| | | | |
|-----------------------|---------------|-----------------------|----------------|
| Electrical Type | Squirrel Cage | Starting Method | Direct On Line |
| Poles | 6 | Rotation | Bi-Directional |
| Mounting | B35 | Motor Orientation | Horizontal |
| Drive End Bearing | 2z-C3 | Opp Drive End Bearing | 2z-C3 |
| Frame Material | Cast Iron | Shaft Type | Keyed |
| Overall Length | 622 mm | Frame Length | 254 mm |
| Shaft Diameter | 42 mm | Shaft Extension | 110 mm |
| Assembly/Box Mounting | R Side | | |
| Outline Drawing | 0216000811 | Connection Drawing | 8442000085 |

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:12/01/2022

4


3

Uncontrolled Copy


2

1

OUTLINE




B




B

A



A

| | | |
|--|----------------------|--------------------|
| DRAWING REVISION B | REVISION BY BISWA | DATE 27/07/2018 |
| ECO ECO-0148344 | APPROVED BY SBD | DATE 27/07/2018 |
| DRAWING UPDATED | | |
| COPYRIGHT REGAL BELOIT AMERICA, INC. ALL RIGHTS RESERVED. PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF REGAL BELOIT AMERICA, INC. ("OWNER") AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED, BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS. | | |



| | | | |
|---------------------------|--------------------------------------|------------------------------|-----------------|
| DRAWN BY SN | marathon™ Motors | | |
| DATE 19/08/2016 | | | |
| APPROVED BY SBD | DESCRIPTION OUTLINE | | |
| DATE 19/08/2016 | 160M FR B35-MTG.TYPE: TCA/QCA-RHS TB | | |
| REFERENCE | MATERIAL | PROCESS/FINISH | |
| THIRD ANGLE PROJECTION | SIZE B | DRAWING NUMBER 0216000811 | SHEET 1 OF 1 |

4

3

2

1

RIGHTS RESERVED. Copy

ECO DESCRIPTION

GEOMETRIC TOLERANCE

| | | |
|------------|---------|------|
| LINEAR DIM | >0~6 | ±0.1 |
| | >6~30 | ±0.2 |
| | >30~120 | ±0.3 |



1. PRESSURE-SENSITIVE ADHESIVE COATED PAPER ON THE BACK OF SELF-ADHESIVE.
2. AT THE END OF YELLOW, WORDS, SYMBOLS, LETTERS ARE BLACK, BORDER IS BLACK.
3. THE TOLERANCE OF THE LINEAR SIZE OF THE TOLERANCE WITHOUT THE TOLERANCE BY THE TABLE.

8WD.442.2017

| | | | | |
|---|------------------------|---|-------------------------------------|----------------|
|  | DRAWN BY SN |  Regal Beloit America, Inc. | | |
| | DATE 16/12/2016 | | | |
| | APPROVED BY SBD | DESCRIPTION CONN DIAGRAM-NAMEPLATE | | |
| | DATE 16/12/2016 | | | |
| | REFERENCE | MATERIAL | | PROCESS/FINISH |
| | THIRD ANGLE PROJECTION | SIZE A | DRAWING NUMBER 8442000085 | |

Model No. TCA7P53A3133GACD01

| U (V) | Δ / Y Conn | f (Hz) | P [kW] | P [hp] | I [A] | n [RPM] | T [Nm] | IE Class | % EFF at __ load | | | | PF at __ load | | | I _A /I _N [pu] | T _A /T _N [pu] | T _K /T _N [pu] |
|----------|---------------|-----------|-----------|-----------|----------|------------|-----------|-------------|------------------|------|-------|-------|---------------|-------|-------|--|--|--|
| 415 | Δ | 50 | 7.5 | 10 | 14.8 | 977 | 72.92 | IE3 | 5/4FL | FL | 3/4FL | 1/2FL | FL | 3/4FL | 1/2FL | 5.5 | 1.9 | 2.5 |
| | | | | | | | | | - | 89.1 | 89.1 | 88.5 | 0.79 | 0.73 | 0.59 | | | |
| | | | | | | | | | | | | | | | | | | |

| | |
|----------------------------------|----------------------------|
| Motor type | TCA |
| Enclosure | TEFC |
| Frame Material | Cast Iron |
| Frame size | 160M |
| Duty | S1 |
| Voltage variation * | ± 10% |
| Frequency variation * | ± 5% |
| Combined variation * | 10% |
| Design | N |
| Service factor | 1.0 |
| Insulation class | F |
| Ambient temperature | -20 to +50 °C |
| Temperature rise (by resistance) | 70 [Class B] K |
| Altitude above sea level | 1000 meter |
| Hazardous area classification | NA |
| Zone classification | NA |
| Gas group | NA |
| Temperature class | NA |
| Rotor type | Aluminum Die cast |
| Bearing type | Anti-friction ball bearing |
| DE / NDE bearing | 6309-2Z / 6209-2Z |
| Lubrication method | Greased for life |
| Type of grease | NA |

| | |
|---|--|
| Degree of protection | IP 55 |
| Mounting type | IM B35 |
| Cooling method | IC 411 |
| Motor weight - approx. | 142 kg |
| Gross weight - approx. | 162 kg |
| Motor inertia | 0.1355 kgm ² |
| Load inertia | Customer to Provide |
| Vibration level | 2.2 mm/s |
| Noise level (1meter distance from motor) | 61 dB(A) |
| No. of starts hot/cold/Equally spread | 2/3/4 |
| Starting method | DOL |
| Type of coupling | Direct |
| LR withstand time (hot/cold) | 15/30 s |
| Direction of rotation | Bi-directional |
| Standard rotation | Clockwise form DE |
| Paint shade | RAL 5014 |
| Accessories | |
| Accessory - 1 | - |
| Accessory - 2 | - |
| Accessory - 3 | - |
| Terminal box position | RHS |
| Maximum cable size/conduit size | 1R x 3C x 35mm ² /2 X M32 x 1.5 |
| Auxiliary terminal box | NA |

I_A/I_N - Locked Rotor Current / Rated Current

T_K/T_N - Breakdown Torque / Rated Torque

T_A/T_N - Locked Rotor Torque / Rated Torque

NOTE

All performance values at rated voltage and frequency.

All performance parameters are subjected to standard tolerance as per IEC 60034-1

* Voltage, Frequency and combine variation are as per IEC60034-1

Technical data are subject to change. There may be discrepancies between calculated and name plate values.


| Efficiency | Europe | China | India | Aus/Nz | Brazil | Global IEC |
|------------|--------|-------|-----------------|--------|--------|------------|
| Standards | - | - | IS 12615 : 2018 | - | - | - |

Model No. TCA7P53A3133GACD01


| Enclosure | U (V) | Δ / Y Conn | f (Hz) | P [kW] | P [hp] | I [A] | n [RPM] | T [kgm] | T [Nm] | IE Class | Amb [°C] | Duty | Elevation [m] | Inertia [kg-m ²] | Weight [kg] |
|-----------|----------|---------------|-----------|-----------|-----------|----------|------------|------------|-----------|-------------|-------------|------|------------------|---------------------------------|----------------|
| TEFC | 415 | Δ | 50 | 7.5 | 10.0 | 14.8 | 977 | 7.44 | 72.92 | IE3 | 50 | S1 | 1000 | 0.1355 | 142 |

Motor Load Data

| Load Point | | NL | 1/4FL | 1/2FL | 3/4FL | FL | 5/4FL |
|--------------|-------|------|-------|-------|-------|------|-------|
| Current | A | 7.2 | 7.7 | 9.3 | 11.6 | 14.8 | |
| Torque | Nm | 0.0 | 17.9 | 36.0 | 54.3 | 72.9 | |
| Speed | r/min | 1000 | 994 | 989 | 983 | 977 | |
| Efficiency | % | 0.0 | 82.8 | 88.5 | 89.1 | 89.1 | |
| Power Factor | % | 7.0 | 40.6 | 59.0 | 73.0 | 79.0 | |

Performance vs Load Chart

Motor Speed Torque Data

| Load Point | | LR | P-Up | BD | Rated | NL |
|------------|-------|------|------|------|-------|------|
| Speed | r/min | 0 | 200 | 868 | 977 | 1000 |
| Current | A | 81.5 | 73.4 | 47.4 | 14.8 | 7.2 |
| Torque | pu | 1.9 | 1.6 | 2.5 | 1 | 0 |

Starting Characteristics Chart

NOTE Refer data sheet for applicable standard and tolerances on performance parameters

 Issued By
 Issued Date




Model No. TCA7P53A3133GACD01

| Enclosure | U (V) | Δ / Y Conn | f [Hz] | P [kW] | P [hp] | I [A] | n [rpm] | T [kgm] | T [Nm] | IE Class | Amb [°C] | Duty | Elevation [m] | Inertia [kg-m ²] | Weight [kg] |
|-----------|----------|----------------------|-----------|-----------|-----------|----------|------------|------------|-----------|-------------|-------------|------|------------------|---------------------------------|----------------|
| TEFC | 415 | Δ | 50 | 7.5 | 10 | 14.8 | 977 | 7.43 | 72.92 | IE3 | 50 | S1 | 1000 | 0.1355 | 142 |

Motor Speed Torque Data

| Load | | FL | I_1 | I_2 | I_3 | I_4 | I_5 | LR |
|----------|----|-------|-------|-------|-------|-------|-------|-----|
| TWT Hot | s | 10000 | 50 | 28 | 21 | 18 | 17 | 15 |
| TWT Cold | s | 10000 | 100 | 55 | 41 | 37 | 33 | 30 |
| Current | pu | 1 | 2 | 3 | 4 | 4.5 | 5 | 5.5 |

Thermal Characteristics Chart



NOTE Refer data sheet for applicable standard and tolerances on performance parameters

Issued By
Issued Date

