

### Nameplate Specifications

|                        |               |                            |                             |
|------------------------|---------------|----------------------------|-----------------------------|
| Output HP              | 3 Hp          | Output KW                  | 2.2 kW                      |
| Frequency              | 50 Hz         | Voltage                    | 230/400 V                   |
| Current                | 4.2 A         | Speed                      | 2889 rpm                    |
| Service Factor         | 1             | Phase                      | 3                           |
| Efficiency             | 85.9 %        | Power Factor               | 0.88                        |
| Duty                   | S1            | Insulation Class           | H                           |
| Frame                  | 90L           | Enclosure                  | Totally Enclosed Fan Cooled |
| Thermal Protection     | No Protection | Ambient Temperature        | 40 °C                       |
| Drive End Bearing Size | 6205          | Opp Drive End Bearing Size | 6205                        |
| UL                     | NO            | CSA                        | NO                          |
| CE                     | YES           | IP Code                    | 66                          |
| Number of Speeds       | 1             | Efficiency Class           | IE3                         |

### Technical Specifications

|                       |               |                       |                |
|-----------------------|---------------|-----------------------|----------------|
| Electrical Type       | Squirrel Cage | Starting Method       | Direct On Line |
| Poles                 | 2             | Rotation              | Bi-Directional |
| Mounting              | B3            | Motor Orientation     | Horizontal     |
| Drive End Bearing     | 2z            | Opp Drive End Bearing | 2z             |
| Frame Material        | Cast Iron     | Shaft Type            | Keyed          |
| Overall Length        | 332 mm        | Frame Length          | 153 mm         |
| Shaft Diameter        | 24 mm         | Shaft Extension       | 50 mm          |
| Assembly/Box Mounting | RHS           |                       |                |
| Outline Drawing       | 0209000821    | Connection Drawing    | 8442000085     |