



Nameplate Specifications

Phase	3	Output HP	15 Hp
Output KW	11.0 kW	Voltage	400 V
Speed	730 r/min	Service Factor	1
Frame	180L	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	No Protection	Efficiency	88.6 %
Ambient Temperature	40 °C	Frequency	50 Hz
Current	24.6 A	Power Factor	0.73
Duty	S1	Insulation Class	F
Drive End Bearing Size	6311	Opp Drive End Bearing Size	6211
UL	No	CSA	No
CE	Yes	IP Code	55
Number of Speeds	1	Efficiency Class	IE3

Technical Specifications

Electrical Type	Squirrel Cage	Starting Method	Direct On Line
Poles	8	Rotation	Bi-Directional
Mounting	B3	Motor Orientation	Horizontal
Drive End Bearing	2z-C3	Opp Drive End Bearing	2z-C3
Frame Material	Cast Iron	Shaft Type	Keyed
Overall Length	750 mm	Frame Length	366 mm
Shaft Diameter	48 mm	Shaft Extension	110 mm
Assembly/Box Mounting	R Side		
Connection Drawing	8442000085	Outline Drawing	0218000764