



Nameplate Specifications

| | | | |
|--------------------|---------------|---------------------|-----------------------------|
| Output HP | 1.5 Hp | Output KW | 1.1 kW |
| Frequency | 60 Hz | Voltage | 208-230/460 V |
| Current | 5.1-4.6/2.3 A | Speed | 1180 rpm |
| Service Factor | 1.15 | Phase | 3 |
| Duty | Continuous | Insulation Class | F |
| Frame | 182T | Enclosure | Totally Enclosed Fan Cooled |
| Thermal Protection | None | Ambient Temperature | 40 °C |
| UL | Recognized | CSA | Y |
| CE | Y | Number of Speeds | 1 |

Technical Specifications

| | | | |
|-----------------------|------------|--------------------|-----------------|
| Electrical Type | POLYPHASE | Starting Method | Across The Line |
| Poles | 6 | Rotation | Reversible |
| Mounting | Rigid Base | Drive End Bearing | Ball |
| Opp Drive End Bearing | Ball | Frame Material | Cast Iron |
| Shaft Type | Keyed | Overall Length | 14.80 in |
| Frame Length | 5.74 in | Shaft Diameter | 1.125 in |
| Shaft Extension | 2.75 in | | |
| Outline Drawing | SS620290 | Connection Drawing | A-EE7308 |

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:10/12/2021