



Nameplate Specifications

Output HP	60 Hp	Output KW	44.8 kW
Frequency	60 Hz	Voltage	208-230/460 V
Current	132/66 A	Speed	3575 rpm
Service Factor	1.15	Phase	3
Duty	Continuous	Insulation Class	F
Frame	364TS	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	None	Ambient Temperature	40 °C
UL	Recognized	CSA	Y
CE	Y	Number of Speeds	1

Technical Specifications

Electrical Type	POLYPHASE	Starting Method	Across The Line
Poles	2	Rotation	Reversible
Mounting	Rigid Base	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Cast Iron
Shaft Type	Keyed	Overall Length	34.57 in
Frame Length	18.50 in	Shaft Diameter	1.875 in
Shaft Extension	3.75 in		
Outline Drawing	SS620284	Connection Drawing	A-EE7308AA

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:10/12/2021