

Nameplate Specifications

| | | | |
|--------------------|---------------|---------------------|-----------------------------|
| Output HP | 2 Hp | Output KW | 1.5 kW |
| Frequency | 60 Hz | Voltage | 200 V |
| Current | 5.75 A | Speed | 1730 rpm |
| Service Factor | 1.15 | Phase | 3 |
| Duty | Continuous | Insulation Class | F |
| Frame | 145T | Enclosure | Totally Enclosed Fan Cooled |
| Thermal Protection | No Protection | Ambient Temperature | 40 °C |
| UL | Recognized | CSA | Y |
| CE | Y | Number of Speeds | 1 |

Technical Specifications

| | | | |
|-----------------------|------------|-------------------|-----------------|
| Electrical Type | POLYPHASE | Starting Method | Across The Line |
| Poles | 4 | Rotation | Reversible |
| Mounting | Rigid Base | Drive End Bearing | Ball |
| Opp Drive End Bearing | Ball | Frame Material | Rolled Steel |
| Shaft Type | Keyed | Overall Length | 14.20 in |
| Frame Length | 6.75 in | Shaft Diameter | 0.875 in |
| Shaft Extension | 2.25 in | | |
| Connection Drawing | A-EE7300 | Outline Drawing | SS620612 |

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:09/16/2022