



### Nameplate Specifications

|                    |               |                     |               |
|--------------------|---------------|---------------------|---------------|
| Output HP          | 1.5 Hp        | Output KW           | 1.1 kW        |
| Frequency          | 60 Hz         | Voltage             | 208-230/460 V |
| Current            | 4.8-4.4/2.2 A | Speed               | 1180 rpm      |
| Service Factor     | 1.15          | Phase               | 3             |
| Duty               | Continuous    | Insulation Class    | F             |
| Frame              | 182T          | Enclosure           | Drip Proof    |
| Thermal Protection | No Protection | Ambient Temperature | 40 °C         |
| UL                 | Recognized    | CSA                 | Y             |
| CE                 | Y             | Number of Speeds    | 1             |

### Technical Specifications

|                       |            |                    |                 |
|-----------------------|------------|--------------------|-----------------|
| Electrical Type       | POLYPHASE  | Starting Method    | Across The Line |
| Poles                 | 6          | Rotation           | Reversible      |
| Mounting              | Rigid Base | Drive End Bearing  | Ball            |
| Opp Drive End Bearing | Ball       | Frame Material     | Rolled Steel    |
| Shaft Type            | Keyed      | Overall Length     | 13.72 in        |
| Frame Length          | 6.75 in    | Shaft Diameter     | 1.125 in        |
| Shaft Extension       | 2.75 in    |                    |                 |
| Outline Drawing       | SS620292   | Connection Drawing | A-EE7308        |

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:11/29/2022