



Nameplate Specifications

| | | | |
|--------------------|-------------|---------------------|-----------------|
| Output HP | 7.5 Hp | Output KW | 5.6 kW |
| Frequency | 60 Hz | Voltage | 208-230/460 V |
| Current | 19.9-18/9 A | Speed | 3500 rpm |
| Service Factor | 1.15 | Phase | 3 |
| Duty | Continuous | Insulation Class | F |
| Frame | 184T | Enclosure | Open Drip Proof |
| Thermal Protection | None | Ambient Temperature | 40 °C |
| UL | Recognized | CSA | Y |
| CE | Y | Number of Speeds | 1 |

Technical Specifications

| | | | |
|-----------------------|------------|-------------------|-----------------|
| Electrical Type | POLYPHASE | Starting Method | Across The Line |
| Poles | 2 | Rotation | Reversible |
| Mounting | Rigid Base | Drive End Bearing | Ball |
| Opp Drive End Bearing | Ball | Frame Material | Rolled Steel |
| Shaft Type | Keyed | Overall Length | 14.72 in |
| Frame Length | 7.75 in | Shaft Diameter | 1.125 in |
| Shaft Extension | 2.75 in | | |
| Connection Drawing | A-EE7308 | Outline Drawing | SS620292 |

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:10/12/2021