



Nameplate Specifications

Output HP	75 Hp	Output KW	56.0 kW
Frequency	60 Hz	Voltage	230/460 V
Current	180/90 A	Speed	1190 rpm
Service Factor	1.15	Phase	3
Duty	Continuous	Insulation Class	F
Frame	405T	Enclosure	Drip Proof
Thermal Protection	None	Ambient Temperature	40 °C
UL	Recognized	CSA	Y
CE	Y	Number of Speeds	1

Technical Specifications

Electrical Type	POLYPHASE	Starting Method	Across The Line
Poles	6	Rotation	Reversible
Mounting	Rigid Base	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Cast Iron
Shaft Type	Keyed	Overall Length	38.78 in
Frame Length	21.25 in	Shaft Diameter	2.875 in
Shaft Extension	7.25 in		
Connection Drawing	A-EE7308AA	Outline Drawing	SS620253

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:10/12/2021