



Nameplate Specifications

Output HP	40 Hp	Output KW	29.8 kW
Frequency	60 Hz	Voltage	208-230/460 V
Current	103-95.5/48 A	Speed	1780 rpm
Service Factor	1.15	Phase	3
Duty	Continuous	Insulation Class	F
Frame	324T	Enclosure	Drip Proof
Thermal Protection	No	Ambient Temperature	40 °C
UL	Recognized	CSA	Y
CE	Y	Number of Speeds	1

Technical Specifications

Electrical Type	Three Phase	Starting Method	Across The Line
Poles	4	Rotation	Reversible
Mounting	Rigid Base	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	T	Overall Length	28.55 in
Frame Length	14.56 in	Shaft Diameter	2.125 in
Shaft Extension	5.25 in		
Connection Drawing	EE7308AA	Outline Drawing	SS620746

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:10/12/2021