



Nameplate Specifications

Output HP	200 Hp	Output KW	149.2 kW
Frequency	60 Hz	Voltage	460 V
Current	215 A	Speed	3582 rpm
Service Factor	1.15	Phase	3
Duty	Continuous	Insulation Class	F
Frame	444TS	Enclosure	Drip Proof
Thermal Protection	None	Ambient Temperature	40 °C
UL	Recognized	CSA	Y
CE	Y	Number of Speeds	1

Technical Specifications

Electrical Type	POLYPHASE	Starting Method	Across The Line
Poles	2	Rotation	Reversible
Mounting	Rigid Base	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Cast Iron
Shaft Type	Keyed	Overall Length	40.83 in
Frame Length	25.98 in	Shaft Diameter	2.375 in
Shaft Extension	4.75 in		
Outline Drawing	SS620256	Connection Drawing	A-EE7341C

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:10/12/2021