



Nameplate Specifications

| | | | |
|--------------------|------------|---------------------|-----------------|
| Output HP | 5 Hp | Output KW | 3.7 kW |
| Frequency | 60 Hz | Voltage | 230 V |
| Current | 25.4 A | Speed | 3520 rpm |
| Service Factor | 1.15 | Phase | 1 |
| Duty | Continuous | Insulation Class | F |
| Frame | 184TC | Enclosure | Open Drip Proof |
| Thermal Protection | No | Ambient Temperature | 40 °C |
| UL | Recognized | CSA | Y |
| CE | Y | Number of Speeds | 1 |

Technical Specifications

| | | | |
|-----------------------|-----------------|-------------------|------------------|
| Electrical Type | Capacitor Start | Starting Method | Across The Line |
| Poles | 2 | Rotation | Counterclockwise |
| Mounting | Rigid Base | Drive End Bearing | Ball |
| Opp Drive End Bearing | Ball | Frame Material | Rolled Steel |
| Shaft Type | Keyed | Overall Length | 16.21 in |
| Frame Length | 12.00 in | Shaft Diameter | 1.125 in |
| Shaft Extension | 2.36 in | | |
| Connection Drawing | 005033.01CY | Outline Drawing | 035907CY |

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:10/12/2021