

Product Information Packet: Model No: V308M2, Catalog No:V308M2 General Purpose Farm Duty Motor, 5.5 HP, 1 Ph, 60 Hz, 230 V, 1200 RPM, 215T Frame, DP

Nameplate Specifications

Output HP	5.5 Hp	Output KW	4.1 kW
Frequency	60 Hz	Voltage	230 V
Current	22 A	Speed	1165 rpm
Service Factor	1	Phase	1
Duty	Continuous	Insulation Class	F
Frame	215T	Enclosure	Drip Proof
Thermal Protection	Manual	Ambient Temperature	40 °C
UL	Recognized	CSA	Y
CE	N	Number of Speeds	1

Technical Specifications

Electrical Type	Capacitor Start Capacitor Run	Starting Method	Across The Line
Poles	6	Rotation	Selective Counterclockwise
Mounting	Rigid Base	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	Keyed	Overall Length	19.31 in
Frame Length	12.40 in	Shaft Diameter	1.375 in
Shaft Extension	3.47 in		
Outline Drawing	037826CY	Connection Drawing	A-EE9048MT-CY

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:09/08/2022