

PRODUCT INFORMATION PACKET



Model No: 93014-23
Catalog No: 93014-23
B-93014-23 TACH/AVTRON/HS35A/14096/.625 SH - HS35AD1CCU1EA000

Regal and Marathon are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E



Nameplate Specifications

Technical Specifications

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:04/05/2025

4								3				2				1											
NOTE: LEAVE COVER PLATE OFF IF IT INTERFERES WITH TEBC FAN.																											
11-05-2014	27	HS35AY1CDU1DA000	2	.6250/.6245 [15.8750/15.8623]	MS CONN	-		D																			
8-11-2014	26	HS35AS1FDU1DA000	2	1.0000/.9995 [25.4000/25.3873]	MS CONN	-		D																			
07-07-2014	25	HS35AY1FCU0EA000	1	1.0000/.9995 [25.4000/25.3873]	MS CONN	1		D																			
04-02-2014	24	HS35A91FCU1EA000	1	1.000/.9995 [25.4000/25.3873]	MS CONN	1		D																			
	23	HS35AD1CCU1EA000	1	.6250/.6245 [15.8750/15.8623]	MS CONN	1		D																			
08-17-2021	22	HS35A41FCU1DA000	2	1.000/.9995 [25.4000/25.3873]	MS CONN	-	A784A	E																			
03-16-2017	21	HS35AY1FCU1DA000	1	1.000/.9995 [25.4000/25.3873]	MS CONN	-	A783A	E																			
	20	HS35A41FCU1DA000	1	1.000/.9995 [25.4000/25.3873]	MS CONN	-		D																			
08-17-2021	19	HS35A41CCU1EA000	1	.6250/.6245 [15.8750/15.8623]	MS CONN	1	A780A	E																			
08-17-2021	18	HS35AY1CCU1EA000	1	.6250/.6245 [15.8750/15.8623]	MS CONN	1	A779A	E																			
08-17-2021	17	HS35AY1FCU1EA000	1	1.000/.9995 [25.4000/25.3873]	MS CONN	1		E																			
02-03-2010	16	HS35A91FWU0EA000	1	1.000/.9995 [25.4000/25.3873]	PIGTAIL	1		D																			
11-06-2009	15	HS35AD1FCU1EA000	1	1.000/.9995 [25.4000/25.3873]	MS CONN	1		D																			
06-23-2009	14	HS35A41FCU1EA000	1	1.000/.9995 [25.4000/25.3873]	MS CONN	1		D																			
04-08-2009	13	HS35A41FAU1DA000	1	1.000/.9995 [25.4000/25.3873]	MS CONN	-		D																			
01-07-2009	12	HS35AD1FWU0EA000	1	1.000/.9995 [25.4000/25.3873]	PIGTAIL	1		D																			
03-29-2008	11	HS35AY1FWU1EA000	1	1.000/.9995 [25.4000/25.3873]	PIGTAIL	1		D																			
03-27-2008	10	HS35AY1CDU1CA000	1	.6250/.6245 [15.8750/15.8623]	MS CONN	-		D																			
04-04-2008	9	HS35AY1FDU1CA000	2	1.000/.9995 [25.4000/25.3873]	MS CONN	-		D																			
02-28-2008	8	HS35AD1FCU1DA000	1	1.000/.9995 [25.4000/25.3873]	MS CONN	1		D																			
	7	HS35AY1FDU1EA000	1	1.000/.9995 [25.4000/25.3873]	MS CONN	1		D																			
A	6	HS35A41FWU0EA000	1	1.000/.9995 [25.4000/25.3873]	PIGTAIL	1	A741	D																			
	5	HS35A41FDU1DA000	2	1.000/.9995 [25.4000/25.3873]	MS CONN	-	A740	D																			
	4	HS35A41CDU1EA000	1	.6250/.6245 [15.8750/15.8623]	MS CONN	1	A739	D																			
	3	HS35AY1FWU0EA000	1	1.000/.9995 [25.4000/25.3873]	PIGTAIL	1	A738	D																			
	2	HS35AY1FDU1DA000	2	1.000/.9995 [25.4000/25.3873]	MS CONN	-	A737	D																			
	1	HS35AY1CDU1EA000	1	.6250/.6245 [15.8750/15.8623]	MS CONN	1	A736	D																			
DASH	VENDORPART NUMBER	FIG	SHAFT SIZE	TERMINATION	MTG. DASH	CAT. No.	REV.																				
TETHER HARDWARE SUPPLIED BY AVTRON																											
								DRAWING REVISION K ECO CR-0003999				REVISION BY SP APPROVED BY SS		DATE 08/13/2021 DATE 08/13/2021		TOLERANCES UNLESS OTHERWISE SPECIFIED: DEC. INCH mm ANGLE .X ±0.1 [±2.5] ±7° 30" .XX ±0.02 [±0.51] .XXX ±0.005 [±0.127] .XXXX ±0.0005 [±0.0127] REMOVE BURRS & BREAK SHARP EDGES: .003/.015 [0.076/.381] X 45° CORNER FILLETS: R.02 [.51] MACHINED SURFACES: 200 INCH 5.1/mm mm SHOWN IN [BRACKETS]				DRAWN BY DRS DATE 10-13-2006 APPROVED BY GK DATE 10-24-2006 REFERENCE		REGAL™ Regal Beloit America, Inc. DESCRIPTION ENCODER AVTRON HS35A MATERIAL PROCESS/FINISH				SIZE B DRAWING NUMBER 93014 SHEET 1 OF 2	
4								3				2				1											

