

PRODUCT INFORMATION PACKET



Model No: 91130-72
Catalog No: 91130-72
B-91130-72 ENCODER HS35R/1.000 SH - HS35R1024H1PA

Regal and Marathon are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E



Nameplate Specifications

Technical Specifications

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:04/05/2025

4

DASH	VENDOR PART NUMBER	REV	SHAFT SIZE	FIG	TERMINATION	MOUNTING DASH
11-13-2000	30	NA	-	1	DBL. PIGTAIL	1
11-13-2000	29	NA	10	1	DBL. PIGTAIL	1
11-13-2000	28	HS35R2048H7R7	-	1	DBL. MS CONN	1
11-13-2000	27	HS35R1024H7R7	10	1	DBL. MS CONN	1
11-13-2000	26	HS35R2048H6R7	-	1	DBL. MS CONN	1
11-13-2000	25	HS35R102486R7	-	1	DBL. MS CONN	1
11-13-2000	24	HS35R204886R7	-	1	DBL. MS CONN	1
10-11-2000	23	USE -25				
08-22-2000	22	HS35R012084P7	-	1	MS CONN	1
	21	HS35R030084P7	10	1	MS CONN	1
06-08-2000	20	HS35R001284P7	-	1	MS CONN	
02-21-2000	19	HS35R2500H4P7	-	1	MS CONN	1
10-07-1999	18	HS35R1024H5N7	-	2	MS CONN	1
02-12-1999	17	SEE DWG 93285 PG 2,-17 FOR PART NUMBER	15	1	PIG TAIL	1
10-22-1998	16	HS35R0512H4P7	15	1	MS CONN	1
05-15-1998	15	HS35R051284P7	-	1	MS CONN	1
05-15-1998	14	HS35R0512H5P7	-	2	MS CONN	
05-15-1998	13	SEE DWG 93285 PG 2,-13 FOR PART NUMBER	15	1	PIG TAIL	1
01-19-1998	12	HS35R2048H4P7	15	1	MS CONN	1
11-05-1997	11	HS35R0250H2P7	-	1	MS CONN	2
10-21-1997	10	HS35R204885P7	-	2	MS CONN	
10-24-2007	9	SEE DWG 93285 PG 2,-9 FOR PART NUMBER	15	1	PIG TAIL	1
10-24-2007	8	HS35R2048H5P7	15	2	MS CONN	
10-24-2007	7	HS35R204884P7	15	1	MS CONN	1
01-23-1997	6	HS35R1024H2P7	15	1	MS CONN	2
01-20-1997	5	HS35R1024H4P7	15	1	MS CONN	1
10-24-2007	4	SEE DWG 93285 PG 2,-4 FOR PART NUMBER	-	1	PIG TAIL	1
	3	HS35R102485P7	15	2	MS CONN	
10-24-2007	2	HS35R102484P7	15	1	MS CONN	1
10-24-2007	1	HS35R1024H5P7	15	2	MS CONN	

3

Uncontrolled Copy

2

1

FIG. 1

DOUBLE CONNECTOR OPTION

40°

DO NOT REVERSE

TERMINATION DIMENSION

TERMINATION	DIMENSION
6 & 7 PIN	3.00 [76.20]
10 PIN	3.38 [85.85]
12 PIN	2.87 [72.90]
CABLE	3.00 [76.20]

TETHER POSITION CAN BE ROTATED IN 15° INCREMENTS

MOUNTING TABLE

DASH	MOUNTING	A	THREAD
1	4.50 [114.30] C'FACE	2.93 [74.42]	3/8
2	8.50 [215.90] C'FACE	3.625 [92.075]	1/2

NOTE: RECOMENDED SHAFT EXTENSION 1.25 [31.75] MIN.

91318 TACHOMETER COVER

IS SUPPLIED WITH TACHOMETER WHERE 10TH DIGIT = 4, 5, 6 OR 7 (EX: HS352048G54B7)

4 = 3/8" BOLTS FOR C'FACE MOUNTS & TENV UNMACHINED BRACKETS

5 = 10-24 SCREWS & T-BOLT FOR FAN GUARD MOUNTING

MOUNTING HARDWARE SUPPLIED BY DYNAPAR

** 91318 TACHOMETER COVER IS NOT SUPPLIED WITH TACHOMETER WHEN 10TH DIGIT = 1 OR 2

* NOT SUITABLE FOR DIV. 2. USE HSD35, DRAWING B-92927, FOR DIVISION 2 REQUESTS.*

COPYRIGHT REGAL BELOIT AMERICA, INC. ALL RIGHTS RESERVED. PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF REGAL BELOIT AMERICA, INC. ("OWNER") AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED, BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS.

TOLERANCES UNLESS OTHERWISE SPECIFIED:

DEC.	INCH	mm	ANGLE
.X	±0.1	[±2.5]	±7° 30"
.XX	±0.02	[±0.51]	
.XXX	±0.005	[±0.127]	
.XXXX	±0.0005	[±0.0127]	

REMOVE BURRS & BREAK SHARP EDGES: .003/.015 [.076/.381] X 45°

CORNER FILLETS: R.02 [.51]

MACHINED SURFACES: 200 INCH/mm 5.1

mm SHOWN IN [BRACKETS]

DRAWN BY TJB

DATE 08-15-2000

APPROVED BY GK

DATE 08-15-2000

REFERENCE

THIRD ANGLE PROJECTION

REGAL Regal Beloit America, Inc.

ENCODER DYNAPAR CONTROLS HS35R

MATERIAL

PROCESS/FINISH

SIZE B

DRAWING NUMBER 91130

SHEET 1 OF 3

4

DASH	VENDOR PART NUMBER	REV	SHAFT SIZE	FIG	TERMINATION	MOUNTING DASH
60	HS35R0240H4P7	11	1.0000/.9995 [25.4000/25.3873]	1	MS CONN	1
59	NA SAME AS -29	-				
58	HS35R0100H515	10	1.0000/.9995 [25.4000/25.3873]	2	6 PIN MS. CONN	
57	HS35R0100H4P7	-	1.0000/.9995 [25.4000/25.3873]	2	MS CONN	
56	SEE DWG 93285 PG 2.-56 FOR PART NUMBER	-	1.0000/.9995 [25.4000/25.3873]	1	PIG TAIL	
55	NA	-	1.1250/1.1245 [28.575/28.5623]	1	PIG TAIL	2
54	HS35R100086R7	-	.6250/.6245 [15.875/15.862]	1	MS CONN	1
53	HS35R102475P7	9	.5000/.4995 [12.700/12.687]	1	MS CONN	1
52	HS35R006084P7	-	.6250/.6245 [15.875/15.862]	1	MS CONN	1
51	NA	9	1.1250/1.1245 [28.575/28.5623]	1	DBL. PIG TAIL	1
50	SEE DWG 93285 PG 2.-50 FOR PART NUMBER	-	1.0000/.9995 [25.4000/25.3873]	1	PIG TAIL	1
49	HS35R10249577	-	15mm (.5906)	1	MS CONN	
48	HS35R0360H4P7	9	1.0000/.9995 [25.4000/25.3873]	1	MS CONN	1
47	HS35R010084P7	-	.6250/.6245 [15.875/15.862]	1	MS CONN	
46	HS35R102484P2	9	.6250/.6245 [15.875/15.862]	1	MS CONNECTOR ONLY NO MATING CONNECTOR	1
45	NA	9	1.1250/1.1245 [28.575/28.5623]	1	PIG TAIL	2
44	HS35R1024J2P2	-	1.1250/1.1245 [28.575/28.5623]		MS CONNECTOR ONLY NO MATING CONNECTOR	2
43	HS35R1024H4P2	9	1.0000/.9995 [25.4000/25.3873]	1	MS CONNECTOR ONLY NO MATING CONNECTOR	1
42	HS35R204884P2	10	.6250/.6245 [15.875/15.862]	1	MS CONNECTOR ONLY NO MATING CONNECTOR	1
41	HS35R2048H4P2	10	1.0000/.9995 [25.4000/25.3873]	1	MS CONNECTOR ONLY NO MATING CONNECTOR	1
40	NA	10	1.1250/1.1245 [28.575/28.5623]	1	PIG TAIL	1
39	HS35R204884P7PS	-	.6250/.6245 [15.875/15.862]	1	MS CONN	1
38	HS35R102484P7	-	.6250/.6245 [15.875/15.862]	1	MS CONN	1
37	HS35R060084P7	-	.6250/.6245 [15.875/15.862]	1	MS CONN	1
36	HS35R150084P7	-	.6250/.6245 [15.875/15.862]	1	MS CONN	1
35	HS35R1500H5P7	-	.6250/.6245 [15.875/15.862]	2	MS CONN	1
34	BOGUS PART NO.	10	.6250/.6245 [15.875/15.862]	1	MS CONN	1
33	HS35R051284P7	-	.6250/.6245 [15.875/15.862]	1	MS CONN	1
32	HS35R250084P7	10	.6250/.6245 [15.875/15.862]	1	MS CONN	1
31	SEE DWG 93285 PG 2.-31 FOR PART NUMBER	-	.6250/.6245 [15.875/15.862]	1	PIG TAIL	1

3

Uncontrolled Copy

2

1

FIG. 1

NOTE: RECOMENDED SHAFT EXTENSION 1.25 [31.75] MIN.

ENCODER DYNAPAR CONTROLS HS35R

91130

2 OF 3

