



### Nameplate Specifications

Output HP	150 Hp	Output KW	111.9 kW
Frequency	60 Hz	Voltage	575 V
Current	134.4 A	Speed	1788 rpm
Service Factor	1.15	Phase	3
Duty	Continuous	Insulation Class	F
Frame	444T	Enclosure	Open Drip Proof
Thermal Protection	None	Ambient Temperature	40 °C
UL	Recognized	CSA	Y
CE	Y	Number of Speeds	1

### Technical Specifications

Electrical Type	POLYPHASE	Starting Method	Across The Line
Poles	4	Rotation	Reversible
Mounting	Rigid Base	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Cast Iron
Shaft Type	Keyed	Overall Length	44.57 in
Shaft Diameter	3.375 in	Shaft Extension	8.50 in
Connection Drawing	A-EE7300U	Outline Drawing	SS620255

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:10/12/2021