

PRODUCT INFORMATION PACKET



Model No: 90817-5J
Catalog No: 90817-5J
B-90817-5J HTR TAPE/158.7-193.9/300V/72"

Regal and Marathon are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E



Nameplate Specifications

Technical Specifications

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:04/05/2025

4				3				Uncontrolled Copy		2		1	
FRAME				OHM ±10% @ 25°C	DIMENSIONS				REV.	NOTES			
NEMA / IEC	DASH	VOLTAGE	WATT	K=1000	A	B	C	D					
48 / 71 56 / 90 140 / 100 180 (6.29")	1A	115	15	792 - 968	.62	12.00	30.00	.06	22				
	1B	230	15	3.15K - 3.85K	.62	12.00	30.00	.06	22				
	1C	460	15	12.69K - 15.51K	.62	12.00	30.00	.06-.08	22				
180(8") / 112 210 / 132 250 / 160 280 (11.0")	2A	115	27	441 - 539	1.00	18.00	30.00	.06	22				
	2B	230	27	1.76K - 2.16K	1.00	18.00	30.00	.06	22				
	2C	460	27	7.02K - 8.58K	1.00	18.00	30.00	.06-.08	22				
280 (12.5") / 180 320 / 200	3A	115	42	284 - 347	1.00	28.00	36.00	.06	22				
	3B	230	42	1.13K - 1.39K	1.00	28.00	36.00	.06	22				
	3C	460	42	4.50K - 5.50K	1.00	28.00	36.00	.06-.08	22				
360 / 225 400 / 250	4A	115	126	94.5 - 115.5	2.00	42.00	42.00	.06	22				
	4B	230	126	378 - 462	2.00	42.00	42.00	.06	22				
	4C	460	126	1.51K - 1.85K	2.00	42.00	42.00	.06-.08	22				
	4D	115	126	94.5 - 115.5	2.00	42.00	72.00	.06	22				
	4E	230	126	378 - 462	2.00	42.00	72.00	.06	22				
	4F	24 DC	126	4.57	2.00	42.00	72.00	.06	22				
	4G	115	126	103 - 126	2.00	38.00	42.00	.06	A				
440 / 280 449 / 280 500 5011 / 315F 5013 / 315D 5000 / 315	5A	115	144	82.8 - 101.2	2.00	48.00	48.00	.06	22				
	5B	230	144	330.3 - 403.7	2.00	48.00	48.00	.06	22				
	5C	460	144	1.32K - 1.62K	2.00	48.00	48.00	.06-.08	22				
	5D	115	144	82.8 - 101.2	2.00	48.00	72.00	.06	22				
	5E	230	144	330.3 - 403.7	2.00	48.00	72.00	.06	22				
	5F	115	144	82.8 - 101.2	2.00	48.00	120.00	.06	22				
	5G	230	144	330.3 - 403.7	2.00	48.00	120.00	.06	22				
	5H	460	144	1.32K - 1.62K	2.00	48.00	120.00	.06-.08	22				
	5J	120	75	172.8 - 211.2	2.00	48.00	72.00	.06	22				
740	6A	115	324	36.7 - 44.9	3.00	72.00	120.00	.06	22				
	6B	230	324	146.9 - 179.6	3.00	72.00	120.00	.06	22				
	6C	460	324	587.8 - 718.4	3.00	72.00	120.00	.06-.08	22				
1000	7A	115	625	19.2 - 23.5	4.50	90.00	120.00	.06	22				

</