

# PRODUCT INFORMATION PACKET



Model No: T10877-12  
Catalog No: T10877-12  
SPRING WASHER

Regal and Marathon are trademarks of Regal Rexnord Corporation or one of its affiliated companies.  
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E




## Nameplate Specifications

## Technical Specifications

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:04/05/2025

LL801 L	7-15-60	3-20-98MC			
	5-19-61A	4-14-00MJ			
CHANGE SHT. NO.	11-6-70				



MATERIAL: SPRING STEEL PER SAE-1070

T10877-16	200	7.909	7.163	.035	.280	.156	123# ±10%	
T10877-15	240	9.509	8.763	.035	.250	.156	148# ±10%	
T10877-14	150	5.817	4.530	.055	.440	.209	217# ±10%	
T10877-13	190	7.325	5.672	.065	.575	.269	300# ±10%	
T10877-12	160	6.173	4.803	.058	.463	.220	240# ±10%	
T10877-11	140	5.408	4.208	.053	.388	.187	200# ±10%	
T10877-10	120	4.627	3.612	.050	.306	.165	160# ±10%	
T10877-8	110	4.300	3.370	.045	.302	.148	140# ±10%	
T10877-7	100	3.917	3.047	.042	.258	.128	120# ±10%	
T10877-6	90	3.519	2.740	.038	.234	.116	100# ±10%	
T10877-5	80	3.118	2.420	.035	.207	.104	88# ±10%	
T10877-4	72	2.816	2.200	.030	.197	.097	65# ±10%	
T10877-3	62	2.420	1.872	.025	.168	.082	45# ±10%	
T10877-2	52	2.028	1.575	.022	.140	.069	35# ±10%	
T10877-1	47	1.819	1.404	.020	.125	.062	30# ±10%	

PART NO.	W.B. CO. NO. O.D. OF BRC. IN MM	A	B	T	H APPROX.	H <sub>1</sub>	LOAD IN LBS DEFLECTED TO H <sub>1</sub>	ACCT. * REV.
		BLANK BEFORE BENDING						

UNLESS OTHERWISE SPECIFIED TOLERANCE  
ON HOLE SIZES PER E2056  
MATERIAL TOLERANCE (%) TO AGREE WITH PUBLISHED STANDARDS.

ON 2 PLACE DECIMALS IS ±.02  
ON 3 PLACE DECIMALS IS ±.002  
ON ALL ANGLES IS ±.5 OF A DEGREE

THE LINCOLN ELECTRIC CO.  
CLEVELAND, OHIO U.S.A.

EQUIP  
TYPE

MISC. USE

SUBJECT BEARING SPRING WASHERS

SCALE NONE DATE 10-4-99

DR JSS CHK DM REF.

SUP'S D'G 6-29-89

SHT. NO. T10877