

PRODUCT INFORMATION PACKET



Model No: 141071.00

Catalog No: 141071.00

..10HP..3465RPM.215JM.DP.230V.1PH.60HZ.CONT.40C.1.15SF.RIGID C.C215K34DK3A.....



Nameplate Specifications

Phase	1	Output HP	10 Hp
Output KW	7.5 kW	Voltage	230 V
Speed	3465 r/min	Service Factor	1.15
Frame	215JM	Enclosure	Drip Proof
Thermal Protection	No Protection	Efficiency	81.5 %
Ambient Temperature	40 °C	Frequency	60 Hz
Current	47.0 A	Power Factor	84
Duty	Continuous	Insulation Class	F
Design Code	L	KVA Code	G
Drive End Bearing Size	309	Opp Drive End Bearing Size	206
UL	Recognized	CSA	Y
CE	N	IP Code	22
Number of Speeds	1		

Technical Specifications

Electrical Type	Capacitor Start Induction Run	Starting Method	Across The Line
Poles	2	Rotation	Selective Counterclockwise
Resistance Main	0 O	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	JM	Assembly/Box Mounting	F1 ONLY
Connection Drawing	A-EE7090JR-LE	Outline Drawing	037643LE-1115

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:09/19/2025



DASH	FR.	C	AG
965	213JM	18.42	14.17
1115	213/15JM	19.92	15.67
1240	213/15JM	21.17	16.92

NOTES:
1. NAMEPLATE TO BE READ FROM C'BOX SIDE OF MOTOR.

				TOLERANCES UNLESS SPECIFIED		 ELECTRIC MOTORS GEARMOTORS AND DRIVES	DRAWN GRB 11/14/08		
				DEC.	INCHES		CHK SK 11/14/08		
				.X	±.1		APPD		
				.XX	±.03		SCALE 1=4.2		
				.XXX	±.005		REF SS86664		
E	ADDED "AJ" DIM OF 7.250 ECO 0083886	GWS 8/21/15		.XXXX	±.0005	MAT'L.		FMF	
NO.	REVISION	BY & DATE	CHK	ANG	± 7'30"	FINISH		PREV	
THIS DRAWING IN DESIGN AND DETAIL IS OUR PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH OUR WORK ALL RIGHTS OF DESIGN AND INVENTION ARE RESERVED THIS IS AN ELECTRONICALLY GENERATED DOCUMENT – DO NOT SCALE THIS PRINT			RFP		CAD FILE 037643		SIZE A	DRAWING NO. PAGE 1 OF 1 037643LE	REV. E
			DIST LB						