



Nameplate Specifications

Phase	1	Output HP	7.50 Hp
Output KW	5.6 kW	Voltage	230 V
Speed	1735 r/min	Service Factor	1.15
Frame	215TVZ	Enclosure	Drip Proof Air Over
Thermal Protection	No Protection	Efficiency	84 %
Ambient Temperature	80 °C	Frequency	60 Hz
Current	34.5 A	Power Factor	85.5
Duty	Continuous	Insulation Class	H
Design Code	L	KVA Code	G
Drive End Bearing Size	309	Opp Drive End Bearing Size	206
UL	Recognized	CSA	Y
CE	N	IP Code	22
Number of Speeds	1		

Technical Specifications

Electrical Type	Capacitor Start Capacitor Run	Starting Method	Across The Line
Poles	4	Rotation	Selective Counterclockwise
Resistance Main	0 O	Mounting	Rigid Base
Motor Orientation	Shaft Up	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	Single Special Extension	Assembly/Box Mounting	W8
Outline Drawing	A-SS89672LE-1115	Connection Drawing	A-EE9048LV-LE

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:09/19/2025