

Nameplate Specifications

Phase	1	Output HP	3 Hp
Output KW	2.2 kW	Voltage	115/230 V
Speed	3500 r/min	Service Factor	1.15
Frame	182JM	Enclosure	Drip Proof
Thermal Protection	No Protection	Efficiency	75.5 %
Ambient Temperature	60 °C	Frequency	60 Hz
Current	32.0/16.1 A	Power Factor	80
Duty	Continuous	Insulation Class	F
Design Code	L	KVA Code	G
Drive End Bearing Size	6207	Opp Drive End Bearing Size	6205
UL	Recognized	CSA	Y
CE	Y	IP Code	22
Number of Speeds	1		

Technical Specifications

Electrical Type	Capacitor Start Induction Run	Starting Method	Across The Line
Poles	2	Rotation	Selective Clockwise
Resistance Main	.342 O	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	JM	Assembly/Box Mounting	F1 ONLY
Connection Drawing	005062.01ME	Outline Drawing	035557-950

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:09/19/2025