

Nameplate Specifications

Phase	3	Output HP	25 Hp
Output KW	18.7 kW	Voltage	575 V
Speed	1180 r/min	Service Factor	1
Frame	324T	Enclosure	TEBC
Thermal Protection	Thermostat	Efficiency	92.4 %
Ambient Temperature	40 °C	Frequency	60 Hz
Current	25.5 A	Power Factor	80
Duty	Continuous	Insulation Class	F
Design Code	A	KVA Code	G
Drive End Bearing Size	312	Opp Drive End Bearing Size	311
CSA	Y	IP Code	54
Number of Speeds	1		

Technical Specifications

Electrical Type	Squirrel Cage Inverter Duty	Starting Method	Inverter Only
Poles	6	Rotation	Reversible
Resistance Main	.28 O	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Cast Iron
Shaft Type	T	Assembly/Box Mounting	F1/F2 CAPABLE
Inverter Load	CONSTANT 2000:1		
Connection Drawing	A-EE7300AK	Outline Drawing	B-SS300361-1150

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:10/24/2025